


Model RSH-ZM



Models RSH7 to 12ZM

Model No.	Outer dimensions			LM block dimensions											H ₃
	Height	Width	Length	B	C	S × l	L ₁	T	K	N	E	Greasing hole d	Grease nipple		
	M	W	L												
RSH 7ZM	8	17	23.4	12	8	M2 × 2.5	13.2	3.4	6.5	1.6	—	1.5	—	1.5	
RSH 9ZM	10	20	30.8	15	10	M3 × 2.8	19.4	4.6	7.8	2.4	—	1.6	—	2.2	
RSH 12ZM	13	27	35	20	15	M3 × 3.2	20.4	4.5	10.6	3.1	—	2	—	2.4	
RSH 15ZM	16	32	43	25	20	M3 × 3.5	26.5	5.5	12.6	2.9	3.6	—	PB107	3.4	


Note) Since stainless steel is used in the LM block, LM rail and balls, these models are highly resistant to corrosion and environment.

Model number coding

2	RSH15Z M	UU	C1	+230L	P	M	-II
No. of LM blocks used on the same rail	Model number	Contamination protection accessory symbol (*1)	Radial clearance symbol (*2) Normal (No symbol) Light preload (C1)	LM rail length (in mm)	Accuracy symbol (*3) Normal grade (No Symbol) High accuracy grade (H) Precision grade (P)	Stainless steel LM rail	Symbol for No. of rails used on the same plane (*4)






(*1) See contamination protection accessory on [A1-380](#). (*2) See [A1-94](#). (*3) See [A1-106](#). (*4) See [A1-37](#).

Note) This model number indicates that a single-rail unit constitutes one set. (i.e., required number of sets when 2 rails are used in parallel is 2 at a minimum.)



Model RSH15ZM

Unit: mm

	LM rail dimensions						Basic load rating		Static permissible moment N-m*					Mass	
	Width		Height	Pitch		Length*	C	C ₀	M _A		M _B		M _C	LM block	LM rail
	W ₁	W ₂	M ₁	F	d ₁ × d ₂ × h	Max	kN	kN						kg	kg/m
	7 ⁰ _{-0.02}	5	4.7	15	2.4 × 4.2 × 2.3	300	0.88	1.37	2.93	20.7	2.93	20.7	5	0.008	0.23
	9 ⁰ _{-0.02}	5.5	5.5	20	3.5 × 6 × 3.3	1000	1.47	2.25	7.34	43	7.34	43	10.4	0.014	0.32
	12 ⁰ _{-0.025}	7.5	7.5	25	3.5 × 6 × 4.5	1340	2.65	4.02	11.4	74.9	10.1	67.7	19.2	0.028	0.58
	15 ⁰ _{-0.025}	8.5	9.5	40	3.5 × 6 × 4.5	1430	4.41	6.57	23.7	149	21.1	135	38.8	0.05	0.925

Note) The maximum length under "Length*" indicates the standard maximum length of an LM rail. (See B1-158.)

Static permissible moment*: 1 block: static permissible moment value with 1 LM block

Double blocks: static permissible moment value with 2 blocks closely contacting with each other